

PATIENT LIFT REFERENCE GUIDE

Types of Patient Lifts

ELECTRIC

Designed for residents who cannot support their own weight.

- Can lower to assist fallen residents off the floor
- Vertical style lifts residents straight up and down for easier positioning

SIT-TO-STAND

Made for residents who can bear at least some of their own weight.

- More dignified and conducive to resident
 involvement
- Features a small footprint for easy storage

Glossary

CRADLE POINTS

Sling attachments. Lifts typically accommodate slings with four or six cradle points.

BASE WIDENING

- Powered base widening only requires the push of a button
- Manual base widening, whether by hand shift or foot pedal, places some strain on the caregiver

BASE CLEARANCE

To maximize effectiveness, consider the base clearance of your lifts to ensure they fit under existing beds.

Important Sling Information

There are a number of full body slings with a variety of characteristics. Take note of each sling's:

- Weight capacity
- Material construction
- Size
- Number of hookup points

NON-POWERED (MANUAL)

- For residents requiring minimal assistance.
 - Allows for quick and easy transfers
 - Features a compact design
 - No batteries required

BATHING

Made for residents who need assistance with bathing.

BASE LENGTH AND WIDTH

Shorter base lengths and widths allow a

around the equipment a resident is being

Full travel height range allows lifting from

lift to be used in tight spaces. The base of the lift should open wide enough to fit

transferred to or from.

the floor.

HEIGHT RANGE

• Allows for efficient transfers by gently and safely lowering or raising residents into or out of a tub or bathing area



Other considerations include:

Padding

- High back section
- Brushed lining to
 prevent sliding
- Waist belt
 Stretch resistance
- Commode
 Opening





© 2015 HDS IP Holding. LLC. All Rights Reserved. For a full description of our terms and conditions, see the back of Catalog V65 or visit hdsupplysolutions.com/terms.

PATIENT LIFT REFERENCE GUIDE

HEALTHCARE SOLUTIONS

E BRAND	PRODUCT NAME	WEIGHT CAPACITY	HEIGHT RANGE	BASE WIDTH	CRADLE POINTS	BASE / UNDERBED CLEARANCE	SCALE Available	FLOOR PICK-UP FEATURE	BATTERIES PER LIFT	WARRANTY	PART #
	I-Lift Power Lift	450 Lb	22.2 To 76.1"	Open: 37.4" Closed: 27.8"	6	4.6"	Yes	Yes	2	3-Year On Lift 1-Year On Electrical Components	602001: See V10, Page 47
	I-Lift Power Plus	450 Lb	22.2 To 76.1"	Open: 37.4" Closed: 27.8"	6	4.6"	Yes	Yes	2	3-Year On Lift 1-Year On Electrical Components	602002: See V10, Page 47
INVAC4RE	Reliant 450	450 Lb	24 To 74"	Open: 41" Closed: 26.5"	6	4.5"	Yes	Yes	1	3-Year On Lift 1-Year On Electrical Components	673400, 673401: See V10, Page 48
Yes, you can.®	Reliant 600	600 Lb	28 To 68"	Open: 41" Closed: 26.5"	6	4.5"	Yes	No	2	3-Year On Lift 1-Year On Electrical Components	673405, 673406: See V10, Page 48
	Jasmine Patient Lift	500 Lb	17 To 74"	Open: 46.75" Closed: 25.75"	6	4.75"	Yes	Yes	2	3-Year On Lift 2-Year On Electronics	676922: See V10, Page 48
O Joerns Hoyer *	Classic Series Deluxe Power Lifter	400 Lb	28 To 77"	24 To 40.5"	6	5"	Yes	No	1	1-Year On Lift, All Components	669373: See V10, Page 50
	Classic Series Power Lifter	700 Lb	23 To 69"	27.5 To 46.25"	6	4.5"	Yes	Yes	1	2-Year On All Mechanical And Electrical Components (Excluding DC Batteries And Casters) 90-Day On DC Batteries And Casters	669374: See V10, Page 48
	Classic Series Power Lifter With Scale	700 Lb	23 To 69"	27.5 To 46.25"	6	4.5"	Yes	Yes	1	2-Year On All Mechanical And Electrical Components (Excluding DC Batteries And Casters) 90-Day On DC Batteries And Casters	669375: See V10, Page 48
	Professional Stature Lift	500 Lb	26.6 To 77.7"	Open: 48.4" Closed: 25.1"	4 Or 6	4.3"	Yes	Yes	1	2-Year On All Mechanical And Electrical Components (Excluding DC Batteries And Casters) 90-Day On DC Batteries And Casters	673924: See V10, Page 49
	Professional Stature Lift With Scale	500 Lb	26.6 To 77.7"	Open: 48.4" Closed: 25.1"	4 Or 6	4.3"	Yes	Yes	1	2-Year On All Mechanical And Electrical Components (Excluding DC Batteries And Casters) 90-Day On DC Batteries And Casters	673926: See V10, Page 49
	Professional Presence Lift	500 Lb	57.5 To 81.3"	Open: 40.1" Closed: 22.8"	4	4.7"	Yes	Yes	1	2-Year On All Mechanical And Electrical Components (Excluding DC Batteries And Casters) 90-Day On DC Batteries And Casters	673925: See V10, Page 49
	Professional Presence Lift With Scale	500 Lb	57.5 To 81.3"	Open: 40.1" Closed: 22.8"	4	4.7"	Yes	Yes	1	2-Year On All Mechanical And Electrical Components (Excluding DC Batteries And Casters) 90-Day On DC Batteries And Casters	673927: See V10, Page 49
drive "	Electric Lift	600 Lb	32 To 74.5"	Open: 41" Closed: 24"	6	4.6"	No	Yes	1	Lifetime Limited On Lift 1-Year On Electrical Components	668032
	Electric Lift	450 Lb	27.5 To 76"	15 To 41"	6	4.5"	No	Yes	1	Lifetime Limited On Lift 1-Year On Electrical Components	668031
INVACARE Yes, you can.º	Reliant 350 Stand-Up Lift	350 Lb	39.5 To 63.75"	Open: 36.75" Closed: 25.75"	2	4.5"	No	No	2	3-Year On Lift 1-Year On Electrical Components	673415, 673416 See V10, Page 51
	Roze Stand-Up Lift	450 Lb	37 To 63.5"	Open: 44" Closed: 26"	2	4.75"	No	No	2	5-Year On Lift 2-Year On Electrical Components	676921: See V10, Page 51
Joerns Hoyer	Classic Hydraulic Lift	400 Lb	28 To 77"	Open: 40.5" Closed: 24"	4 Or 6	5.5"	No	No	N/A	1-Year On Lift, All Components	669372: See V10, Page 52
drive "	Manual Patient Lift	400 Lb	21 To 64"	Open: 41" Closed: 24"	4 Or 6	6"	No	No	N/A	Limited Lifetime On Frame 1-Year On Pump	669085
INVACARE Yes, you can.º	IH1200 Stretcher Lift With Stretcher Seat 80.5"L x 18"W	350 Lb	30" Vertical Travel	34.5"	N/A	5"	Yes	No	2	1-Year On Lift, All Components	673745
	IH1900 Lift/Transporter With Stretcher Seat 18"H x 16.5"W x 16"	350 Lb	23" Vertical Travel	28.5"	N/A	5"	Yes	No	2	1-Year On Lift, All Components	673767, 673738 See V10, Page 50